



MYSOWIPES – ALCOHOL IMPREGNATED WIPES

ITEM NO. 0052 (10 x 50 WIPES), 0053 (300 WIPES)

WHAT MYSOWIPES DO

OUR LOW PARTICULATE POLYESTER CELLULOSE WIPES ARE A VERSATILE WIPE THAT CAN BE USED IN A VARIETY OF SETTINGS. THESE 0.2 MICRON FILTERED ALCOHOL BLEND WIPES ARE IMPREGNATED WITH IPA 70% V/V IN WFI QUALITY WATER AND VIRTUALLY INDESTRUCTIBLE IN THE HAND.

AVAILABLE IN A 50-WIPE RESEALABLE PACK OR 300-WIPE RESEALABLE TUB.

EACH WIPE IS LARGE AND EXTREMELY ABSORBENT, MEASURING 25 X 28 CM WITH A BASIS WEIGHT OF 66 GSM. A HEAT-SEALED FOIL BAG IS USED INSIDE THE CONTAINER TO HELP PREVENT ALCOHOL LOSS BEFORE AND DURING USE.

How TO USE:

1. EACH PACK CONTAINS A Z-FOLDED STACK WITH COMPLETELY SEPARATE SHEETS, FOR QUICK, EASY REMOVAL OF INDIVIDUAL WIPES.
2. INSIDE THE CONTAINER THE IMPREGNATE WIPES ARE HERMETICALLY SEALED INSIDE A FOIL BAG TO PREVENT IMPREGNANT LOSS PRIOR TO FIRST USE. THE IMPREGNATED WIPES ARE SELF-DISPENSING ONCE THE INNER FOIL BAG IS OPENED AND THE FIRST CLOTH HAS BEEN DRAWN FROM THE CENTRE OF THE ROLL AND FED THROUGH THE OPENING IN THE LID.
3. RE-CLOSE THE LID MOUNTED CAP AFTER USE IN ORDER TO MINIMISE EVAPORATION OF THE IMPREGNANT

OVERALL PACK SIZE AND WEIGHT HAVE BEEN SELECTED TO PERMIT EASE OF HANDLING AND PORTABILITY.

MYSOWIPES ARE SUITABLE FOR USE ON ALL INDUSTRIAL HARD SURFACES

PARTICULAR AREAS SUGGESTED FOR THE USE OF MYSOWIPES INCLUDE:

- FILLING AND PACKING LINES
- IN-PLANT CONVEYOR SYSTEMS
- LABORATORIES

HEALTH AND SAFETY

SEE SEPARATE SAFETY DATA SHEET

THE INFORMATION CONTAINED IN THIS DATA SHEET IS ACCURATE TO THE BEST OF OUR KNOWLEDGE AND BELIEF. NO WARRANTY IS, HOWEVER, GIVEN OR IMPLIED. CONSULT AGMA LTD CONCERNING ALL NON-STANDARD APPLICATIONS.

ISSUE NO. 1-08/26